

Analogue Dual Zone Monitor

CHQ-DZM(SCI)



Features

- ▶ Single loop address
- ▶ Supports two independent zones of conventional detectors
- ▶ Both zones fully monitored for short/open circuit
- ▶ Requires an auxiliary 24 V dc supply
- ▶ DIN rail version available
- ▶ Both models feature an integral short-circuit isolator
- ▶ Approved by LPCB

Description

Model CHQ-DZM(SCI) is a Dual Circuit Zone Controller designed to allow up to 60 conventional detectors (30 on each zone) to be interfaced to Hochiki's ESP analogue addressable system. The unit also features a Schottky Diode line continuity option, when used in conjunction with the optional LCMU.

Full monitoring against malfunction or disconnection, together with a self-test feature through the ESP protocol, ensure the integrity of the CHQ-DZM(SCI) at all times. The CHQ-DZM(SCI) utilises simple DIL switches for reliable addressing. It is available as an OEM version (as illustrated above) and also as a DIN Rail mountable module (CHQ-DZM/DIN(SCI)). Both models feature an integral short-circuit isolator.

When Resistive EOL option is chosen the conventional zone on the CHQ-DZM(SCI) does not support any line continuity options, therefore if Call Points are being interfaced they should be wired at the beginning of the zone.

Specification

Ordering Code	CHQ-DZM(SCI) (as shown) CHQ-DZM/DIN(SCI) (DIN module)		
Operating Voltage	17 - 41 V dc		
Low Power Mode (typ)	110 μ A		
Quiescent Current (typ)	330 μ A		
Current Consumption (External)	(Quiescent) 2 mA, (Alarm) 70 mA (both zones in fire)		
Capacitance on Zone	0.3 μ F Max		
Resistance on Zone	50 Ω Max		
Current in short-circuit	8 mA		
Max short-circuit current (Loop)	1 A		
Operating Temperature Range	-10 $^{\circ}$ C to +50 $^{\circ}$ C		
Storage Temperature Range	-30 $^{\circ}$ C to +60 $^{\circ}$ C		
E.O.L. Device Options	TE-RH-E (<i>supplied</i>), 6K8 resistor or LCMU (6K8) (<i>not supplied</i>)		
Output Rating	24 V dc 8.5 mA		
Quantity per Zone	DCA, DFB, DFE - No limit, SLG, SLK, SLR, SIF, SIH, SIJ, DCC, DCD, DFJ - 30 max, SPB-ET, SPC-ET or SRA-ET- 3 max, HF-24 - Only one and no other detectors, DRD-E - 15 max, CCP-E - No limit		
Weights (g) & Dimensions (mm)	CHQ-DZM(SCI)	350	L=157 x W=127 x D=35 (CHQ Module plus Lid) D=79 (CHQ Module plus Lid plus CHQ-BACKBOX) (add 235 to module weight when using CHQ-BACKBOX) L108 x W119 x D24 (CHQ DIN Module)
	CHQ-DZM/DIN(SCI)	130	

Hochiki Europe (UK) Ltd. reserves the right to alter the specification of its products from time to time without notice. Although every effort has been made to ensure the accuracy of the information contained in this document it is not warranted or represented by Hochiki Europe (UK) Ltd. to be a complete and up-to-date description.